


MOMENTS®

TWO-HANDLE WIDESPREAD LAVATORY FAUCET WITH BRASS SPOUT




MODEL NUMBER:

2506.821 Widespread Lavatory

Metal Speed Connect Pop-up drain.

Metal Lever handles, Individual base escutcheon.



GENERAL DESCRIPTION:

Cast brass valve bodies with flexible hose connections for 6" to 12" (152mm to 305mm) installations. 1/4 turn washerless ceramic disc valve cartridges. Brass spout. One-half inch male inlet shanks with brass coupling nuts. 20 inch (500mm) long flexible stainless steel drain cable is pre-assembled to spout. Metal Speed Connect® drain body with 1-1/4 inch (32mm) tail piece. 1.5 gpm/5.7L/min. maximum flow rate.

PRODUCT FEATURES:

Brass Construction: Durable. Ideal for prolonged contact with water. Provides the finest surface for application of colors and finishes.

Ceramic Disc Valve Cartridges: Assures a lifetime of drip-free performance.

Lead Free: Faucet contains $\leq 0.25\%$ total lead content by weighted average.

Exclusive Speed Connect Metal Drain:

- Fewer parts. Installs in less time.
- No adjustments required seals the first time, every time.
- Flexible stainless steel cable installs effortlessly in tight spaces.

Finish: Available in Polished Chrome.

SUGGESTED SPECIFICATION:

Two handle widespread lavatory faucet shall feature cast brass valve bodies with flexible hose connections for 6" to 12" installations. Shall also feature 1/4 turn washerless ceramic disc valve cartridges. Shall also feature a metal drain body with stainless steel cable actuation. Fitting shall be American Standard Model #2506.821.002.

© 2013 AS America, Inc.




MOMENTS® TWO-HANDLE WIDESPREAD LAVATORY FAUCET

WITH BRASS SPOUT

CODES AND STANDARDS

These products meet or exceed the following codes and standards:

ANSI A117.1 ASME A112.18.1 CSA B 125 NSF 61/Section 9 and Annex G



		Finish Options
Product		Polished Chrome
Number	Description	002
2506.821	Lavatory faucet with Metal Speed Connect® Pop-up drain. Metal Lever handles.	



Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for the physically challenged.

AERATOR MODIFICATIONS***	Parts Suffix**
0.5gpm (1.9Lpm) PCA* Spray	F05
0.5gpm (1.9Lpm) Vandal Resistant PCA Spray	V05
1.0gpm (3.8Lpm) PCA Aerator	F10
1.0gpm (3.8Lpm) Vandal Resistant PCA Aerator	V10
1.5gpm (5.7Lpm) Vandal Resistant PCA Aerator	V15

^{*}PCA — Pressure Compensating

^{**}To modify a product, add suffix after the 4th digit (ex. 2064F05101.002)

^{***}Modified product models are **NOT** WaterSense certified.