

RANDALL[™] PRESSURE BALANCE TUB & SHOWER TRIM




- Cast brass spout & valve
- Ceramic disc valve cartridge
- Adjustable hot limit safety stop
- Pressure balance cartridge maintains constant output temperature in response to changes in relative hot and cold supply pressures
- Concealed mounting hardware
- Integral diverter
- Available with cross or lever handle


CODES AND STANDARDS

Meets or Exceeds ASME A112.18.1/CSA B125.1/ASSE 1016

AVAILABLE FINISHES Polished Chrome Brushed Nickel	FINISH CODE 100 144	DESCRIPTION Pressure Balance Tub & Shower Trim	PRODUCT NUMBER
Platinum Nickel	150	— Cross Handle — Lever Handle Tub/Shower Rough Valve	D35102640.XXX D35102600.XXX D35000600.191
NOTE: ALL DIMENSIONS ARE TYPICAL TO B/S WITH DIVERTER	FINISHED WALL	1-5/8" TO 3-1/4" (41 TO 83mm) OPTIONAL TO FINISHED FLOOR USUALLY BETWEEN 72" AND 84" (1829 TO 2134mm) INLETS (STOPS)	Cross Lever
74" FOR HEAD CLEARANCE (OPTIONAL) (1880 mm)	"SEE ILLUSTRATION"	OUTLETS 1/2" NPT 5-3/4" (146 mm)	

(200mm)





18"

(457mm)

OPTIONAL

TOP OF-TUB RIM LEVER CROSS

-BOTTOM OF TUB

4" (102mm)

