

## Luxura® 6032 Skirted Air Bath Bathtub

| Letter | Description                     | English                        | Metric                         |
|--------|---------------------------------|--------------------------------|--------------------------------|
| -      | Drain Location                  | Left / Right Hand              | Left / Right Hand              |
| -      | Blower Location                 | Opposite end of drain location | Opposite end of drain location |
| -      | Cutout                          | N/A                            | N/A                            |
| -      | Total Weight                    | 805 lb                         | 366 kg                         |
| -      | Floor Loading                   | 60 lb/ft <sup>2</sup>          | 293 kg/m <sup>2</sup>          |
| -      | Operating Gallons (Min/Max)     | 33 Gal / 50 Gal                | 125 L / 189 L                  |
| -      | Product Weight                  | 88 lb                          | 40 kg                          |
| L      | Outer Length                    | 60.00"                         | 1524 mm                        |
| W      | Outer Width                     | 32.00"                         | 813 mm                         |
| H      | Overall Height                  | 20.25"                         | 514 mm                         |
| A      | Overflow Height                 | 17.50"                         | 445 mm                         |
| B      | Long Edge to Drain Center       | 10.25"                         | 257 mm                         |
| C      | Short Edge to Drain Center      | 15.38"                         | 391 mm                         |
| D      | Drain Shoe Length               | 8.25"                          | 206 mm                         |
| E      | Flange Height                   | 1.00"                          | 25 mm                          |
| F      | Deck Width                      | 2.63"                          | 67 mm                          |
| G      | Service Access Dimensions       | See Illustration Below         | See Illustration Below         |
| I      | Floor Cutout for Drain          | 12.00" x 4.00"                 | 305 mm x 102 mm                |
| J      | Interior Dimensions J(W) x J(L) | 19.00" x 44.50"                | 483 mm x 1130 mm               |
| -      | Number of Injectors             | 34                             | 34                             |

### NOTE

The overall dimensions are nominal with a tolerance of +0 and -.25" (6mm).

Electrical Specifications


(Each component requires a separate, dedicated GFCI protected circuit)

Blower


120V 15A 60HZ

## Key Dimensions


Left End Drain / Right Side Blower




Left End Blower / Right Side Drain




\*Deck width reflects only area indicated on detail.



Side View  
(LH Drain)



End View  
(LH Drain)



**NOTE:** Drawings not to scale.