



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
8.00"	21.50"	8.00"
<u>BP Height</u>	<u>BP Width</u>	
4.25"	6.00"	
<u>Hanging Weight</u>		
4.00 lb		

Lamping:

Incandescent MB	0 Rated Lumens
3.00 60W MB	Color Temperature
180 total watt	
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
5.57 lb	9.80"	9.80"	24.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209108462	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location

Additional:

MB (Not Included)
Lighting Direction: BOTH