



## Hide-A-Lite 4

## Undercabinet

Type \_\_\_\_\_

-31

P8683-31



### Finish

Catalog  
No.

Black

### Dimensions (Inches)

A

B

C


P8683-31

-31

5

2

1



### Specifications:

#### General

- Black (-31) finish
- Dimmable using an electronic low-voltage dimmer

#### Mounting

- Undercabinet mount

#### Electrical

- High power factor >95%
- Hard wire 100W 24V zero load transformer
- Maximum operating temperature -20° C to +90° C
- Electronic circuit design with short circuit and overload protection with auto shut down/reset

- Sound rated A, emits no audible noise
- Intergrated 5-pin female connector for direct connection to the 1st LED strip in the run
- Electrically isolated, flame resistant, UL 2108 approved plastic enclosure
- Pre-wired

#### Labeling

- ETL Dry location listed

Progress Lighting  
701 Millennium Blvd.  
Greenville, South Carolina  
29607

www.progresslighting.com

Rev. 01/14