

FEATURES & SPECIFICATIONS

INTENDED USE

The LED Globe provides an attractive low-cost lighting solution in residential and light commercial applications. Ideal for use in foyers, hallways, bedrooms, closets, offices, utility work areas, stairways and many other areas.

CONSTRUCTION

Popular globe shape fixture with choice of white, polished brushed nickel or bronze housing. White glass globe diffuser provides widespread, uniform illumination. Three side-mounted thumb screws provide easy access for cleaning.

OPTICS

Produces 635 lumens (4000K) at 50,000 hours of life.

ELECTRICAL

Fixture operates at 120 volts, 60Hz. Standard input = 8.7 watts, 60 lumens per watt.

Actual wattage may differ by \pm 5% when operating at 120V \pm 10%.

Works with most standard incandescent dimmers (see list of approved dimmers).

INSTALLATION

All mounting hardware included.

LISTINGS

UL Certified to US and Canadian safety standards and listed suitable for damp locations.

WARRANTY

5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

Catalog Number	
Notes	
Туре	



Decorative Indoor

LED Globe

Flush Mount

ESSENTIALS COLLECTION





C	rifirn	+:
MIP	(((mm

(A) Width: 6 (15.2) (B) Extension*: 7 (17.7) Weight: 1.8 lbs.





Example: FMGLOL 6 7840 WH

All dimensions are inches (centimeters) unless otherwise indicated.

ORDERING INFORMATION For shortest lead times, configure product using **bolded options**.

Series	Module/CRI/Color Temperature	Finish		
FMGLOL 6 6" Flush mount LED globe, 6" diameter	7840 > 80 CRI, 4000K 7835 > 80 CRI, 3500K ¹ 7830 > 80 CRI, 3000K 7827 > 80 CRI, 2700K ¹	WH White BNP Polished brushed nickel BZ Bronze		

Replacement parts: Order as separate catalog number.

DGLOB6 Glass diffuser, white

Notes


 Minimum 90-day lead time for non-standard color temperatures; minimum 50 order quantity.


DECORATIVE INDOOR FMGLOL

^{*} Extension from ceiling.

LED Globe Flush Mount


LIGHTING FACTS





PHOTOMETRICS

FMGLOL 6 7830 WH, 526 delivered lumens, test no. LTL 26585S tested in accordance to IESNA LM-79.



pf рс pw 0 1 2 3 ACR 5 6 6 7 8 9 10

Coefficients of Utilization												
			2	20%								
	80%	% 70% 50%		70%		70%		Zonal Lumen Summary				
70%	50%	30%	50%	30%	10%	50%	30%	10%	Zone	Lumens	% Lamp	% Fixture
108	108	108	100	100	100	86	86	86	0° - 30°	35	6.8	6.8
94	88	82	81	76	71	68	64	60	0° - 40°	62	12.0	12.0
84	74	66	68	61	55	57	51	47	0° - 60°	136	26.2	26.2
75	64	54	58	50	44	49	42	37	0° - 90°	281	54.2	54.2
68	55	46	51	43	36	43	36	31	90° - 120°	137	26.5	26.5
62	49	39	45	36	30	38	31	26	90° - 130°	172	33.2	33.2
57	43	34	40	32	26	34	27	22	90° - 150°	219	42.3	42.3
53	39	30	36	28	22	30	24	19	90° - 180°	237	45.8	45.8
49	35	27	32	25	19	27	21	16	0° - 180°	518	100.0	100.0
45	32	24	30	22	17	25	19	15				
42	29	21	27	20	15	23	17	13				

SUGGESTED DIMMERS

DECORATIVE INDOOR:

The FMGLOL is designed to operate with most standard Triac Based dimmers and is not compatible with 0-10v dimming systems. The following is a list of dimmers tested and does not imply any guarantee or warranty of compatibility with a particular application. Unlisted dimmers do not imply non-compatibility.

Part number(s)				
CT-600P/CT-603P				
DV-600P/DV-603P				
CTCL-153P				
DVCL-153P				
AYCL-153P				
DVELV-300P				
R50-IPL06				
6615-P				
HCL453PTCCCV6				
ISD 600 I 120				



FMGLOL