# **Wide Angle Float Switch**



## **Product Features**

- For use with sump & utility pumps
- Non-mercury activated switch
- 10ft cord with piggyback plug
- 120 Volts AC
- Max pump running current: 10 amps
- Includes stainless steel mounting clamp
- Flexible 18 gauge cable, 2 conductor (UL, CSA) SJOW, water-resistant, (CPE)


- 33 feet or 13 PSI maximum water depth
- Float housing made from high impact, corrosion resistant, polypropylene for use in water temperatures up to 140°F
- Float dimensions:
  4.83" L x 2.74" diameter



#### PF92000SJE

# **Product Specifications**

Pumping Range Chart							
Tether Length	3.5"	6"	9"	12"	15"	18"	22"
Pumping Range	8"	11"	15"	21"	28"	31"	36"



\* All measurements are nominal. Please verify before actual installation.

### **Warranty and Codes**

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO float switch carries a 1 year warranty when installed in residential applications. See owners manual for warranty details.

This PROFLO float switch carries a year limited warranty. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless it is agreed in writing to do otherwise.

