

ESTATE® PEDESTAL SINK FINE FIRECLAY

BARRIER FREE

ESTATE® PEDESTAL SINK

0900.800 Faucet holes on 8" (203mm) centers (Illustrated)
0900.400 Faucet holes on 4" (102mm) centers
0900.100 Center hole only
Fine fireclay

- · Classic styled rectangular pedestal lavatory
- · Rear overflow
- Supplied with mounting kit
- Right Height® for greater comfort during use
- Faucet ledge with large deck area (faucet not included)
- Design coordinates with ESTATE® VORMAX™ Toilet
- Basin has flat bottom to also allow use as an **above** counter sink or a drop-in sink (with u-shaped cut out)

Nominal Dimensions:

24" x 20" x 36" (610 x 508 x 902mm)

0900.008	Pedestal	top-8"	(203mm) centers
0900.004	Pedestal	top-4"	(102mm) centers
0900.001	Pedestal	top-ce	nter hole only
0029.000	Pedestal	only	

Bowl sizes:

15-1/16" (383mm) wide, 12-5/16" (313mm) front to back, 5" (127mm) deep

Compliance Certifications -

Meets or Exceeds the Following Specifications:

• ASME A112.19.2 - 2008/CSA B45.1-08


To Be Specified: ☐ Color: ☐ White ☐ Linen
☐ Faucet Finish:
☐ Supplies:
☐ 1-1/4" Trap:
☐ Nipple:




SEE REVERSE FOR ROUGHING-IN DIMENSIONS

^{*} See faucet section for additional models available







NOTES: * DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAPS

ARE SUGGESTED.

▼ PEDESTAL ANCHORING SCREWS NOT INCLUDED.
■ SUITABLE FOR REINFORCEMENT ONLY. ACTUAL DIMENSIONS MUST

BE TAKEN FROM FIXTURE.
FITTING NOT INCLUDED AND MUST BE ORDERED SEPARATELY.
PROVIDE SUITABLE REINFORCEMENT FOR ALL WALL SUPPORTS.
INSTALLATION INSTRUCTIONS SUPPLIED WITH LAVATORY.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerance established by ANSI Standard A112.19.2 These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.