solid state

PROGRESS

Close-To-Ceiling


Energy Star® Qualified

Bingo

Type ______

P3737

	Finish						
Catalog No.	Brushed Nickel	Venetian Bronze	Light Source		Dimensions (Inches)		
				Α	В	с	
P3737	-0930K9	-7430K9	LED (included)	24	3-1/2	45-3/4	



Specifications:

<u>General</u>

- White acrylic diffusers: 11" dia.
- Plated Brushed Nickel (-0930K9), Venetian Bronze (-7430K9) finishes
- Steel construction
- Complies with "Americans with Disabilities Act" ADA
- Energy Star® qualified
- LED Module is replaceable
- 5 year warranty
- Matching fixtures P3695, P3747 and P3756

<u>Mounting</u>

- Wall or ceiling mount
- Ceiling pancovers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

<u>Electrical</u>

• Pre-wired

<u>Light Engine</u>

- 17w / 0.15 amps at 120VAC, 60Hz
- Lumens: 1211 per module
- 71.2 lumens per watt
- TM-21/L70 lifetime 60,000 hour life
- 3000K CCT
- 90 CRI
- Dimmable to 10% brightness, see list below for known compatible controls:
 - Lutron: DVCL-153P, MAELV-600, NTELV-300, SPSELV-60
 - Leviton: AWRMG-EAW
 - We do not recommend using digital dimmer controls
 - Compatibility with incandescent dimmers varies by load, due to this factor, we recommend ELV type dimmers for best performance.

<u>Labeling</u>

• cCSAus Damp location listed



Greenville, South Carolina

Progress Lighting

29607

701 Millennium Blvd.