



solid state

Bingo
Energy Star® qualified


Close-To-Ceiling

Type _____

-0930K9 -7430K9

P3747 ☐ ☐

Catalog No.	Finish		Light Source	Dimensions (Inches)		
	Brushed Nickel	Venetian Bronze		A	B	C
P3747	-0930K9	-7430K9	LED array (included)	23-3/4	3-3/8	24-1/8



Specifications:

General

- White acrylic diffusers: 11" dia.
- Plated Brushed Nickel (-0930K9), Venetian Bronze (-7430K9) finishes
- Steel construction
- Complies with "Americans with Disabilities Act" - ADA
- Energy Star® qualified
- LED Module is replaceable
- 5 year warranty
- Matching fixtures P3695, P3737 and P3756

Mounting

- Wall or ceiling mount
- Ceiling pancovers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- Pre-wired

Light Engine

- 17w / 0.15 amps at 120VAC, 60Hz
- Lumens: 1211 per module
- 71.2 lumens per watt
- TM-21/L70 lifetime 60,000 hour life
- 3000K CCT
- 90 CRI
- Dimmable to 10% brightness, see list below for known compatible controls:
 - Lutron: DVCL-153P, MAELV-600, NTELV-300, SPSELV-60
 - Leviton: AWRMG-EAW
 - We do not recommend using digital dimmer controls
 - Compatibility with incandescent dimmers varies by load, due to this factor, we recommend ELV type dimmers for best performance.

Labeling

- cCSAus Damp location listed

Rev. 10/14



Progress Lighting
701 Millennium Blvd.
Greenville, South Carolina
29607

www.progresslighting.com