

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P2112-15

Oasis

Two-light bath from the Oasis Collection can turn any bath area into a spa-like environment. The chrome arm and back plate reflect beveled detailing paired with square fluted etched glass shades.

Category: Bath & Vanity

Finish: Polished Chrome (plated)

Construction: Steel construction

Glass: Etched glass square fluted shades

Width: 14-5/8"

Height: 7-3/4"

Depth: 6-3/4"

H/CTR: 5-1/2"

Glass: 5-1/16" top square,

2-1/2" bottom square

Height: 4-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Mounts in "up" or "down" position</p> <p>Back plate covers a standard 4" hexagonal recessed outlet box</p> <p>6-7/16" W.Includes socket ring tool, 4-1/2", 1"</p>	<p>Threaded socket ring secures glass</p> <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 2</p> <p>100W Medium Base</p> <p>E26 sockets</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion Bath and Vanity, fixtures are available</p>