

Features

- Fixture-mount design.
- Includes 1.5 V AA batteries.

Material

Brass construction.

Technology

- Electronic infrared sensor with WAVE technology for accurate
- Slow-closing piston technology.

Installation

Intended for toilet installations with 1-1/2" spud coupling

Optional Accessories

GP1118986 Flushometer Extension Kit K- 10313 12" Supply Line Sleeve K- 13716 24" Tailpiece



ADA **CSA B651 OBC**

Codes/Standards

ASME A112.18.1/CSA B125.1 **ASSE 1037** ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description


CP Polished Chrome







WAVE DC 1.28 GPF WC Flushometer K-10673-SV



Technical Information

All product dimensions are nominal.

Pressure and Supply Requirements

Fixture flow rate min: 25 gpm (94.6 lpm) Fixture pressure max 80 psi (551.6 kPa)

(static):

Power source: AA 1.5 V, included

Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

