

## **Features**

- Fixture-mount design.
- Includes 1.5 V AA batteries.

## Material

Brass construction.

## **Technology**

- Electronic infrared sensor with TriPoint™ technology for accurate activation.
- Slow-closing piston technology.

## Installation

 Intended for toilet installations with 1-1/2" spud coupling connection

# **Optional Accessories**

GP1118986 Flushometer Extension Kit K- 10313 12" Supply Line Sleeve K- 13716 24" Tailpiece



ADA CSA B651 OBC

## Codes/Standards

ASME A112.18.1/CSA B125.1 CSA B64 ASSE 1037 ADA ICC/ANSI A117.1 CSA B651 OBC

# **KOHLER® One-Year Limited Warranty**

See website for detailed warranty information.

## **Available Color/Finishes**

Color tiles intended for reference only.


Color Code Description

CP Polished Chrome





# Tripoint™ DC 1.28 GPF WC Flushometer K-10956-SV



## **Technical Information**

All product dimensions are nominal.

# **Pressure and Supply Requirements**

Fixture flow rate min: 25 gpm (94.6 lpm) Fixture pressure max 80 psi (551.6 kPa)

(static):

Power source: AA 1.5 V, included

#### **Notes**

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

