


# Z1202-N4 EZCARRY<sup>®</sup> ADJUSTABLE VERTICAL HIGH PERFORMANCE SIPHON JET NO-HUB WATER CLOSET CARRIER SYSTEM

### SPECIFICATION SHEET

TAG





Product	Approx.
Number	Wt.
	lbs [kg]
Z1202-N4	65 [29]

Note:

- 1. Z coupling, Min. 'P' Dim. Obtainable=2 [51] EZ-Set<sup>™</sup>Coupling, Min. 'P' Dim. Obtainable=4-1/4 [108] or 2-1/16 [52] for 12 [305] NPT
- 2. Feet bolted to floor using min. 1/2 [13] dia. anchors.
- 3. Rear anchor foot required for secure installation.
- 4. 2 [51] No-Hub vent connection regularly furnished on right hand side. Left hand available when specified (Suffix -VL)
- 5. Auxiliary inlet available right (-JR) or left (-JL) or both sides (-JJ) when specified.

## ENGINEERING SPECIFICATION: ZURN Z1202-N4

EZCarry<sup>®</sup> vertical siphon jet water closet carrier system with high performance waterway and 4" [102mm] no-hub connections. System includes Dura-Coated cast iron main fitting with hydro-mechanically optimized sweep and extended 2" [51mm] vent, adjustable gasketed faceplate, universal floor mounted pre-fab slotted foot supports, heavy-duty 1/2" [13mm] rear anchor tie down, fixture bolts, trim, stud protectors, bonded "Neo-Seal" gasket, and corrosion resistant, adjustable 3" [76mm] dia. X 6" [152mm] coupling with integral test cap designed to increase flow velocity and line carry. EZCarry® system complies with the requirements of ASME A112.6.1M up to a 500 lbs [227 kg] static load rating.

## **OPTIONS** (Check/specify appropriate options)

Z1202-N4 4 [102] No-Hub Stack, Single Inlet, 2 [51] Right Hand Vent

#### PREFIXES

- D.C.C.I. System with Zurn ZZ Adjustable Coupling\* Ζ
- ZQ D.C.C.I. System with NPT Faceplate, Non-Adjustable Coupling

#### SUFFIXES

SOLLIVES			
A	Auxiliary Support Assembly	JJ	Two 2 [51] Auxiliary Inlets
	(For 'P' Dim. Greater than 18 [457])	JL	2 [51] Left-Hand Auxiliary Inlet
CC	Corrosion Resistant Cast Iron Coupling	JR	2 [51] Right-Hand Auxiliary Inlet
	(2-1/4 [57] to 12 [305])	M	Auxiliary Foot Support
CE	EZ-Set <sup>™</sup> Coupling (NPSM 6 [152] ,12 [305] or custom)		(for 'P' Dim. 10 thru 18 [254 thru 457])
	(NPT 12 [305] or custom)	RYK	Unistrut Pre-Fab Foot Support
-CL	Custom Length Standard Coupling with Integral Test Cap	RYK17	One Piece Unidtrut Pre-Fab Foot
	(Specify Length 4, 8, 10, 12 [102, 203, 254, 305])	VL	Left Hand Vent Connection
-0.5	2-1/4 [57] Polymer Coupling with Integral Test Cap	VP	Vandal-Proof Trim
00	Floor Mounted, Back Outlet Fixture Support	-45	Finishing Frame for Siphon Jet System
		-50	Flush Valve Supply Support for Water Closets
G	Galvanized Cast Iron	00	

\* Regularly furnished unless otherwise specified.

Zurn Industries, LLC | Specification Drainage Operation 1801 Pittsburgh Avenue, Erie, PA U.S.A. 16502 · Ph. 855-663-9876, Fax 814-454-7929 In Canada | Zurn Industries Limited 3544 Nashua Drive, Mississauga, Ontario L4V 1L2 · Ph. 905-405-8272, Fax 905-405-1292 www.zurn.com

Rev. J Date: 05/08/17 136824 C.N. No. Prod. | Dwg. No. Z1202-N4