robern

AiO Cabinet Double Door - Specification Sheet

Features

- Dimmable LED task lighting with on/off touch switch built into the door front
- AiO Light Engine is a mix of 3200K and 6500K LED this design allows 55 footcandles on the users face and produces 32W of light - the LEDS are CRI90
- AiO cabinet can be paired with all M Series mirrored and decorative glass side kits
- Quiet close Safeseal® Gasket
- Mirrored interior with 6 adjustable glass shelves
- Includes magnetic tool holder
- Includes removable magnetic multi-positioning magnifying mirror
- Includes installation hardware for recess mounting
- Can be recessed or surface mounted (surface mounting kit required)
- Includes two USB charging outlets and three 120VAC outlet
- Lighted Interior built inside of door

Construction

- Satin anodized aluminum body and door frame
- Tri-view/multi mirror design rear of cabinet and both sides of both doors
- Concealed finger pull-door edge
- Blum 170° self-closing hinges
- \bullet Safeseal ${\scriptstyle\scriptscriptstyle \circledcirc}$ Gasket with sealed corners on cabinet body
- Adjustable shelving at 2" (51 mm) increments
- Single field wire into electrical shelf Front access serviceability
- Interior Illumination

Codes/Standards Applicable

• Electric Option Models are ETL certified to: UL 962

CSA Standard C22.2 No. 68

Dimensions

Height: 30" (762 mm) Width: 35-1/4" (895 mm) Depth: 4-5/8" (117 mm), 7/8" (22 mm) Project from wall when recessed

Options

• Robern Audio

Installation Options

Recessed Mount - Rough Opening – 29-1/4" H x 34-1/2" W x 4" D (743 mm H x 876 mm W x 102 mm D) Surface Mount - Reference Surface Mount Kit when ordering MSMK30D4P – Plain Mirror Kit MSMK30D4## – Decorative Glass Kit

5	
s s	
2 2	
•	
4	1

AC3630D4P2L

Model Number Key								
AiO Series	Cabinet	Width	Height	Depth	Door Style	Hinge Side	Options	
А	С	36"	30"	D4	P2 = Double	L = Left	Blank = Without Robern Audio A = Robern Audio	

Electrical System


- 120 VAC 60HZ 20A
- Field wire location as shown in drawing
- \circ 1/2" conduit (Ø 7/8" actual) electrical knockout location shown below
- Included field wire cable clamp


Optional Accessories

- Glass Bins
- Swing out Magnifying Mirror SOMM

Robern Audio

- Vibrating Glass Technology Resulting in a virtually hidden system
- Wide Dispersion Almost 160 degrees from the door surface
 Plustooth® Connection
- Bluetooth[®] Connection
- Range: Up To 30 feet / 9.1 meters (depending on interference)
- 2 Channel Stereo
- 20 Watts / Channel
- Supports most Android and iOS devices: Smartphones, PCs, Tablets, and other Bluetooth® enabled devices. Volume controlled by device.
- Audio amplifier with Bluetooth connectivity for wireless streaming of audio input
- Plays your music or audio preferences and selections from any Bluetooth enabled device.





Wall

