Specifications

PFXC9011 TECOPA SINGLE HANDLE KITCHEN FAUCET WITH PULL-DOWN SPRAY HEAD



Product Features

- Ceramic disc cartridge
- Metal lever handle
- 2 Function sprayhead with pause
- · Single hole or 3-hole sink installation with included optional deck plate
- PFXC9011CP/BN Max flow rate: 1.8 gpm (6.8L/min) at 60 psi
- PFXC9011LFBN Max flow rate: 1.0 gpm (3.7L/min) at 60 psi
- Lifetime limited warranty
- Meets ASME : A112.18.1
- NSF 61 compliant
- cUPC/IAPMO listed
- Lever handle meet ADA compliant

Model Numbers

PFXC9011CP (1.8 gpm)	Chrome
PFXC9011ZBN (1.8 gpm)	PVD Brushed nickel
PFXC9011MB (1.8 gpm)	Matte black
PFXC9011LFZBN (1.0 gpm)	PVD Brushed nickel

Available Parts

OBPF63538502* Sprayhead (1.8gpm) PFXC9011SPRY* Sprayhead (1.0gpm)

Note: 1.0 gpm sprayheads available as optional low flow sprayheads for faucet PFXC9011CP/BN. PFXC9011LFBN is available as a full faucet with 1.0 gpm flow rate.




PFXC9011CP



Specifications *PFXC9011 TECOPA SINGLE HANDLE KITCHEN FAUCET WITH PULL-DOWN SPRAY HEAD*



Product Specifications



* All measurements are nominal. Please verify before actual installation.

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. This product meets ASME: A112.18.1. *Compliant with lead content requirements of US Senate Bill S.3874*



©2024 Ferguson Enterprises, LLC. FG 03/24