Specifications

PFWSC5240 Two Handle Lavatory Faucet




- · Ceramic disc cartridges
- · Metal lever handle
- \cdot Requires 3-hole sink with 4" on-center
- \cdot With metal pop-up
- · 100% factory pressure tested
- \cdot Max. flow rate: 1.2 gpm (4.5 L/min) at 60 psi
- \cdot EPA WaterSense approved
- · cUPC/IAPMO listed
- \cdot ADA compliant

Model Numbers

PFWSC5240CP	Chrome
PFWSC5240ZBN	PVD brushed nickel
PFWSC5240NORB	Oil rubbed bronze

Product Specifications



*All measurements are nominal. Please verify before actual installation.

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications.

Compliant with lead content requirements of California AB 1953 and Vermont S.152.



©2022 Ferguson Enterprises, LLC 0422 3672185



PFWSC5240CP

FERGUSON.COM/PROFLO

