PFWSC4744S

SINGLE HANDLE LAVATORY FAUCET

Product Features

- 4" centerset installation
- Flow rate: 1.2 GPM
- Metal lever handle
- Ceramic disc cartridge
- Less pop-up
- Max deck thickness: 1-1/2"
- 30" flexible nylon Neoperl supply lines
- Brass construction
- Meets ANSI:A112.18.1M
- NSF 61 compliant
- cUPC/IAPMO listed
- WaterSense rated
- With adjustable temperature limit stop

Model Numbers

PFWSC4744SCP chrome

Available Parts

PF32067417 Cartridge

Optional Accessories

PFGD10	Grid Drain
PFX14320	0.5 GPM aerator –insert only
PFX14321	1.0 GPM aerator –insert only

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. This product meets ANSI: A112.18.1M. *Compliant with lead content requirements of US Senate Bill S.3874.



PFWSC4744SCP

PROFLO

Product Specifications





