
Specifications

PFXC1180 PFXC1180LS **Two Handle Kitchen Faucet**



- · Ceramic cartridges · Metal lever handles
- · Max. flow rate: 1.5 gpm (5.7 L/min) at 60 psi
- · 100% factory pressure tested
- · cUPC/IAPMO listed
- · ADA Compliant

Model Numbers

PFXC1180CP-with side spray PFXC1180LSCP-less side spray Chrome Chrome


PFXC1180CP


Product Specifications


PFXC1180

9 5/16* 11/16

Ø 2° (Ø 51mm) 1-20UNEF-2A 1/2-14NPSM-2A







*All measurements are nominal. Please verify before actual installation.

Warranty and Codes

10 1/4" (261mm)

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. Compliant with lead content requirements of California AB 1953 and Vermont S.152.



©2022 Ferguson Enterprises, LLC 0422 3672185

FERGUSON.COM/PROFLO





PFXC1180LS