
TAG \_\_\_\_\_

Dimensional Data (inches and [ mm ]) are Subject to Manufacturing Tolerances and Change Without Notice



	Approx.			
A-Pipe Size		C	Е	Wt. Lbs.
NL	NH	O	ı	[kg]
2 [51]	3 [76]	4-1/8 [105]	2-3/4 [70]	5 [2]
3 [76]	4 [120]	5-1/8 [130]	2-3/4 [70]	8 [4]
4 [102]		6-1/8 [156]	2-3/4 [70]	10 [5]
5 [127]	6 [152]	7-1/4 [184]	3-5/8 [92]	15 [7]
6 [152]		8-1/4 [210]	3-5/8 [92]	17 [8]
8 [203]	8 [203]	9-1/4 [235]	3-5/8 [92]	22 [10]

## **ENGINEERING SPECIFICATION:** ZURN Z1402

Tuf-Top non-adjustable floor cleanout with Dura-Coated cast iron body, with gas and watertight ABS tapered thread plug, and round scoriated cast iron heavy-duty secured cover and frame.

**OPTIONS** (Check/specify appropriate options)

· · · · · · · · ·	(Specify size/type) <b>OUTLET</b> 5, 102, 127, 152, 203] NH No-Hub [51, 76, 102, 127, 152, 203] NL Neo-Loc		<b>'E' BODY HT. DIM.</b> See Chart See Chart
ZB [ ZN [	Dura-Coated Cast Iron* D.C.C.I. with Polished Bronze Light-Duty Top (Deduct 7 D.C.C.I. with Polished Nickel Bronze Light-Duty Top (D D.C.C.I. with Polished Stainless Steel Heavy-Duty Top	educt 1/2 [13	3] from 7/8 [22] Dim.)
-CM (	Bronze Plug Carpet Marker Round ZB or ZN Top with Dex-o-Tex Flange (2,3,4,5 [51,76,102,127] only) Galvanized Cast Iron Heavy-Duty Veneer Top (Add 1/8 [3] to 7/8 [22] Dim. for (ZB and ZN only) Neo-Loc Test Cap Gasket (2,3,4 [51,76,102] NL Bottom Outlet Only) Red unless otherwise specified.	T VP	Square Top Vandal-Proof Screws

Zurn Industries, LLC | Specification Drainage Operation
1801 Pittsburgh Avenue, Erie, PA U.S.A. 16502 · Ph. 855-663-9876, Fax 814-454-7929
In Canada | Zurn Industries Limited
3544 Nashua Drive, Mississauga, Ontario L4V 1L2 · Ph. 905-405-8272, Fax 905-405-1292

www.zurn.com

Rev. I

Date: 09/28/2017 C.N. No. 138019

Prod. | Dwg. No. Z1402