

Service Sink / Mop Sink Faucets


TAG:

B-0667-RGH

Service Sink Faucet

Architect/Engineering Specifications:

Wall mount mixing faucet with rough chrome plated brass body, vacuum breaker, rough chrome plated brass spout with pail hook and garden hose male outlet, compression cartridges with spring checks, lever handles, 1/2" NPT female adjustable inlets with built-in service stops, and upper support rod. Certified to ASME A112.18.1/CSA B125.1, NSF 61 - Section 9, NSF 372 and ASSE 1001. Meets ADA ANSI/ICC A117.1 requirements.




Features & Benefits:

- Wall mount mixing faucet with rough chrome plated brass body
- Vacuum breaker spout with pail hook & 3/4" garden hose male outlet
- · Lever handles with color coded indexes
- Quarter-turn Eterna cartridges with spring checks to prevent cross flow of water
- 1/2" NPT female adjustable arm inlets with Ø2" flanges and built-in service stops
- Adjustable centers from 2 1/4" to 8 1/4" above or below centerline
- Upper support rod
- Material: Rough chrome plated brass body & spout and chrome plated metal handles

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)
- ASSE 1001 (VB)



Performance Data:

Pressure: 20 - 125 psiTemperature: 40 °F - 140 °F

Flow Rate: 14.37 GPM @ 60 psi







Optional Handles Option

- ☐ 4" Wrist Action
- □ Lever (Standard)
- □ 4-Arm
- **Optional Cartridges With Checks**

□ Quarter-Turn Cerama w/ Check Valve

□ Quarter-Turn Eterna w/ Spring Check (Standard)







T&S BRASS AND BRONZE WORKS, INC.



