




IRON BODY GAS VALVES - PLUG STYLE

10687B FLAT HEAD LOCKWING TAMPERPROOF


Cast iron body, bronze plug manually operated 175 PSIG natural, manufactured, or propane gas valve for use in above ground gas piping systems in ambient temperatures between -20°F to 150°F. Iron body valves considered full port of flow.



- Inlet: FNPT Thread
- Outlet: FNPT Thread
- Sizes: 1/2", 3/4", 1", 1 1/4", 1 1/2", 2"

~ DIMENSIONS ~					
SIZE	A	B	C	D	E
1/2	2.80	1.40	1.50	3.06	.87
3/4	3.14	1.57	1.74	3.49	.94
1	3.37	1.69	1.85	3.85	1.12
1 1/4	3.88	1.94	2.28	4.75	1.37
1 1/2	4.62	2.31	2.67	5.43	1.62
2	5.62	2.81	2.96	5.82	1.87

- Iron Body - Less Check
- Bronze Plug
- Relubable Plug



Threads per ANSI/ASME B1.20.1

Manufactured to the guidelines set forth in ASME B16.33.

NOTE: All A.Y. McDonald plug style gas valves are factory set.
DO NOT TAMPER WITH BOTTOM NUT.

A.Y. McDONALD MFG. CO. • P.O. BOX 508 • DUBUQUE, IA 52004-0508
800-292-2737 • FAX 800-832-9296 • sales@aymcdonald.com • www.aymcdonald.com
 (Gas Valves3 8/11)