This unit offers anti-siphon protection.

The Woodford Model 25 drains as handle is shut off <u>even</u> <u>if hose is attached</u>. This faucet is designed for outside residential water service applications and intended for irrigation purposes.

SPECIFICATIONS:

MODEL 25 - Approved under ASSE Standard 1019-B and listed by IAPMO®. MeetsGovernment Specification WW-541b Type 205.

Vacuum Breaker - Anti-Siphon

NIDEL® model 34HA with 3/4" male hose thread. Approved under ASSA Standard 1011. Canadian Standards Association and listed by IAPMO®.

FEATURES:

EXTERIOR FINISH - Brass

VALVE - Molded nitrile suitable for hot water.

NOZZLE - 3/4" male hose thread.

NO LEAD SOLDER - All solder joints.

PLUNGER - Hemispherical cushion type.

STEM SCREW - DELRIN®

HEAD NUT - Brass


HANDLE - Metal. (Optional Tee Key)

INLETS - As shown.

MAX PRESSURE - 125 p.s.i.

MAX TEMPERATURE - 120° F

NOTICE - To close and drain, turn handle clockwise until seated and water drains out of the drain hole or faucet may freeze and burst. Vacuum Breaker replacement is recommended every 3-5 years.



Wall Thickness (inches)

 4
 6
 8
 10
 12
 14
 16
 18
 20
 22
 24

 2.0
 2.1
 2.2
 2.3
 2.4
 2.5
 2.7
 2.9
 3.1
 3.3
 3.5

Shipping Wt. (lbs)

Approx. Shipping Weight Each

*Overall Length Dimension: Add wall thickness and inlet option length shown in chart at right.


For Installation / Troubleshooting Instructions go to www.woodfordmfg.com or call 1-800-621-6032

Anti-Siphon Automatic Draining Freezeless Wall Faucet Model 25


WOODFORD



Inlet Descriptions








15/16 1/2" PEX Tube Fitting PX3 INLET 3/4" PEX Tube Fitting

When ordering, specify model, inlet and wall thickness.



MODEL 25 PARTS LIST				
ITEM	PART#	DESCRIPTION		
1	30234	Handle Screw		
2	30438	I.D. Ring - Model 25		
3	30239	Wheel Handle - Metal		
4	30241	Head Nut - Brass		
5	30236	Drain Guard		
6	30245	Head Nut Gasket		
7	30238	Stem Screw		
8	35280	Drain Valve Assembly		
9	303XX	Operating Rod (See Chart)		
10	30230	Plunger Assembly		
11	34HA-BR	34HA Vacuum Breaker - brass		
	RK-25	Repair Kit (Includes items 1, 3-8 & 10)		

OPERATING ROD DIM "A"				
Wall Thickness	Length	Part No.		
4	4-7/16"	30304		
6	6-7/16"	30306		
8	8-7/16"	30308		
10	10-7/16"	30310		
12	12-7/16"	30312		
14	14-7/16"	30314		
16	16-7/16"	30316		
18	18-7/16"	30318		
20	20-7/16"	30320		
22	22-7/16"	30322		
24	24-7/16"	30324		



OPERATING ROD ASSEMBLY INCLUDES ITEMS 1 THRU 10				
Wall Thickness	Overall Length	Part No.		
CC	5"	35501		
4	8"	35504		
6	10"	35506		
8	12"	35508		
10	14"	35510		
12	16"	35512		
14	18"	35514		
16	20"	35516		
18	22"	35518		
20	24"	35520		
22	26"	35522		
24	28"	35524		



Manufactured under one or more of the following U.S. Patents: 3,414,001; 4,178,956; 4,316,481; 4,532,954; D216,790; D216,791; D277,365; D277,366; Canada Patents: 852,529; 865,995; 1,146,438

For more information contact...

WOODFORD MANUFACTURING COMPANY