NuTone

DESCRIPTION

GRILLE:

- Contemporary styled grille complements modern decor
- White polymeric grilles can be painted to match any decor •

MOTOR:

- · Motor assembly offers fast, easy "twist-lock" installation
- Permanently lubricated, thermally protected, plug-in motor
- Specially designed fan blade stays in balance will not distort •

HOUSING:


- · Installs easily in walls or ceiling
- Galvanized steel housing, 25 gage
- Built-in backdraft damper •
- Fits 31/4" x 10" duct •
- Adjustable mounting brackets span from 14" to 24" •

SPECIFICATIONS

[VOLTS	AMPS RPM		SONES	CFM	DUCT
[120	1.5	1725	5.0	160	3¼" x 10"




HVI-2100 CERTIFIED RATINGS comply with new testing technologies and procedures prescribed by the Home Ventilating Institute. for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. static pressure, based on tests conducted in a state-of-the-art test laboratory. Sones are a measure of humanly-perceived loudness, based on laboratory measurements.



Side Dischage Fan

MODEL 8310



ARCHITECT'S SPECIFICATION

Ventilator shall be NuTone Model 8310.

Ventilator shall have compact galvanized steel housing.

Motor assembly shall be removable and permanently lubricated. RPM shall not exceed 1725.

Air delivery shall be no less than 160 CFM and sound levels no greater than 5.0 Sones. All air and sound ratings shall be certified by HVI. Units shall be U.L. listed.

INSTALLATION

Complete installation instructions are included with each Fan.

Broan-NuTone LLC Hartford, Wisconsin www.broan-nutone.com 800-558-1711

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date