# Efficiency™

Top-mount Kitchen Sink

**K-5948-3**

## Features

- 33-inch minimum base cabinet width.
- KOHLER cast iron.
- Top-mount.
- Acid-resistant enamel finish.
- Double (large/medium) compartment.
- Three faucet holes.
- 33" (838 mm) x 22" (559 mm)

## Recommended Accessories

K- 9000 P-Trap

## Optional Accessories

K- 6000 Sink Rack
K- 6521 Sink Basket
K- 8801 Sink Strainer



## Codes/Standards

ASME A112.19.1/CSA B45.2

## KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

## Available Color/Finishes


*Color tiles intended for reference only.*

| Color | Code | Description |
|---|---|---|
| | 0 | White |
| | 96 | Biscuit |
| | 47 | Almond |
| | 7 | Black Black™ |

# Efficiency™

Top-mount Kitchen Sink

**K-5948-3**




## Technical Information

All product dimensions are nominal.

| | |
|---|---|
| Bowl configuration: | Large/medium |
| Installation: | Top-mount |
| Cutout: | Top-mount, 31-7/8" x 20-3/4" (810 mm x 527 mm) with 1" (25 mm) radius corners |
| Bowl area (Left) | Length: 16" (406 mm)<br>Width: 19" (483 mm)<br>Bowl depth: 6-3/4" (171 mm) |
| Bowl area (Right) | Length: 12" (305 mm)<br>Width: 16" (406 mm)<br>Bowl depth: 6-3/4" (171 mm) |
| Number of deck holes: | 3 |
| Faucet hole(s): | 1-3/8" (35 mm) |
| Drain hole: | 3-7/8" (98 mm) |

## Notes

Install this product according to the installation guide.