

# Fairfax® Kitchen Sink Faucet K-12171

### **Features**

- Metal construction.
- One-piece, self-contained ceramic disc valve allows both volume and temperature control.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- High-temperature limit setting for added safety.
- 9" (229 mm) swing spout reach.
- 2.2 gal/min (8.3 l/min) maximum flow rate [max at 60 psi (4.14 bar)].

## **Optional Accessories**

12001



ADA CSA B651

### Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 DOE - Energy Policy Act 1992 ADA ICC/ANSI A117.1 CSA B651 All applicable US Federal and State material regulations

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Color/Finishes


Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	РВ	Vibrant® Polished Brass
	G	Brushed Chrome
	BN	Vibrant® Brushed Nickel
	VS	Vibrant® Stainless
	BV	Vibrant® Brushed Bronze
	BX	Vibrant® Brazen Bronze
	СВ	Polished Chrome with Vibrant® Polished Brass Accents





# Fairfax® Kitchen Sink Faucet K-12171



### **Technical Information**

All product dimensions are nominal. Spout reach: 9" (229 mm)

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 60 psi (4.1 bar)

### **Notes**

Install this product according to the installation guide.

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

