




BRONZE LOW PRESSURE GAS VALVES - PLUG STYLE

10584 SQUARE HEAD WITH CHECK - BOSTON PATTERN

(with double stake nut)

Bronze body and plug manually operated low pressure natural or propane gas valve for use indoors on house piping system between the meter outlet and the inlet connection of the gas appliance at ambient temperatures of 32 to 125 degrees Fahrenheit.

- Inlet: FIP Thread
- Outlet: FIP Thread
- Sizes: 1/2", 3/4", 1", 1 1/4", 1 1/2", 2"




2 PSIG



1/2" & 3/4" valves manufactured to:




B16.44 5 PSIG



1/2" & 3/4" bottom check

~ DIMENSIONS ~

SIZE	A	B	C	D	E
1/2	1	1	.406	1.297	1.266
3/4	1.156	1.156	.469	1.594	1.391



All other sizes top check

~ DIMENSIONS ~

SIZE	A	B	C	D	E
1	1.375	1.375	.469	1.781	1.563
1 1/4	1.609	1.609	.688	2.063	1.938
1 1/2	1.688	1.688	.781	2.25	2.094
2	2.188	2.188	1	2.563	2.313

NOTE: All A.Y. McDonald plug style gas valves are factory set.
DO NOT TAMPER WITH BOTTOM NUT.

A.Y. McDONALD MFG. CO. • P.O. BOX 508 • DUBUQUE, IA 52004-0508
800-292-2737 • FAX 800-832-9296 • sales@aymcdonald.com • www.aymcdonald.com
 (Gas Valves1 2/09)