



**Toccata™**  
Top-mount Kitchen Sink  
**K-3347L-3**

**Features**

- 36-inch minimum base cabinet width.
- 19-gauge stainless steel.
- Top-mount.
- Double (high/low) bowl.
- 4-1/8-inch left depth and 7-inch right depth.
- With SilentShield® sound-absorption technology.
- Three faucet holes on left side.
- 33" (838 mm) x 22" (559 mm)

**Optional Accessories**

K- 6139 Sponge Caddy  
K- 8801 Sink Strainer  
1177161 Installation Clip Kit

**Components**

Product includes:  
1177160 Hardware Kit, Top-mount




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Bowl configuration:	High-low
Installation:	Top-mount
Cutout:	Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1/2" (13 mm) radius corners
Bowl area (Right)	Length: 21" (533 mm) Width: 15-1/4" (387 mm) Bowl depth: 7" (178 mm)
Bowl area (Left)	Length: 7-1/4" (184 mm) Width: 15-1/4" (387 mm) Bowl depth: 4-1/8" (105 mm)
Number of deck holes:	3
Faucet hole(s):	1-7/16" (37 mm)
Drain hole:	3-5/8" (92 mm)

## Notes

Install this product according to the installation guide.