

### Features

- Vitreous china.
- Elongated bowl.
- 11" (279 mm) minimum rough-in.
- 1-1/2" rear spud.
- 2-1/4" (57 mm) glazed trapway.
- 1.28 gpf (4.8 lpf) or 1.6 gpf (6.0 lpf) depending on flushometer specified.
- 11-3/8" (289 mm) x 10-3/8" (264 mm) water area.
- 26" (660 mm) x 14-1/2" (368 mm) x 16-1/2" (419 mm).

### Recommended Accessories

- K- 4670-C Commercial Toilet Seat
- K- 4670-CA Commercial Toilet Seat

### Components

Additional included component/s: Spud, and Bolt caps (pair).



ADA

CSA B651

OBC

### Codes/Standards




ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC


### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Color/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond



Bowl shape:	Elongated front
Flush type:	Siphon jet
Spud size:	1-1/2", Inlet, Rear
Trap passageway:	2-1/4" (57 mm)
Water surface size:	11-3/8" x 10-3/8" (289 mm x 264 mm)
Rim to water surface:	6" (152 mm)
Rough-in:	11" (279 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Min static pressure: 35 psi (241.3 kPa)  
Max static pressure: 80 psi (551.6 kPa)  
Min flow rate: 25 gpm (94.6 lpm)

The Model Plumbing Codes require the installation of elongated open-front toilet seats on public bathrooms.