


Shower System C-96-1-RX14X-G **Specification Submittal**







Feature Highlights


- Symmons commercial series shower system
- Symmons Temptrol[®] pressure balancing mixing valve with adjustable stop screw to limit handle turn
- Dial thermometer hermetically sealed with shatter proof face, color coded bimetal thermometer
- Showerhead #4-137 single mode, cast brass with adjustable flood / mist spray
- Showerhead mounting arm and flange
- Flow rate 2.5 gpm (9.5 L/min)
 Optional lower flow rate restrictor available
- Polished chrome finish (standard)

Model Numbers

- ☐ C-96-1-RC14X-G Shower System with Symmons Temptrol_® pressure balancing mixing valve
- ☐ C-96-1-RC14X-G-TRM
 Shower Trim only, valve must be ordered separately

Handle Options / Modifications

Append appropriate -suffix to model number.



-LAM Lever handle

Warranty

- Limited Lifetime to the original end purchaser in consumer installations.
- 5 years for commercial installations


Options / Modifications

Append appropriate -suffix to model number.

- -X Symmons Temptrol pressure balancing mixing valve includes integral service stops to allow water shut-off for service
- -IPS 1/2 inch female IPS connections on Symmons Temptrol® mixing valve
- -REV Reverse coring in valve for back to back installations; hot on right, cold on left, available with (-X) integral stops only
- -2.0 2.0 gpm (7.6 L/min) flow rate restrictor
- ☐ 🅜 -1.5 1.5 gpm (5.7 L/min) flow rate restrictor
 - l -L/HD Showerhead not included
 Includes showerhead arm and flange only

Standards / Certifications

ASME A112.18.1-2005/CSA B125.1-05



Symmons Industries, Inc. = 31 Brooks Drive = Braintree, MA 02184 (800) 796-6667, (781) 848-2250 = Fax (800) 961-9621, (781) 664-1300 Website: www.symmons.com = Email: customerservice@symmons.com

