



Torino Fixed Rail TRRF Series

Features

This decorative dimmable fixed rail features reliable high-performance LEDs. Available in satin nickel or rubbed bronze. Heads swivel and pivot to direct light where needed and remains cool to the touch when lit. Applications that this fixture could fit well include: kitchens, retail environments, and anywhere that needs highlighted illumination. The fixture mounts to a standard junction box (not included). These fixtures mount to the ceiling or wall.

Construction

The canopy is 22-gauge stamped steel and the rail is made of 20-gauge steel tube. Power supply connections must be made inside a junction box (not included).

Finish

The canopy, rail, and individual rail heads are plated in a satin nickel finish with a clear lacquer topcoat or painted rubbed bronze.

Diffuser

Frosted acrylic.

Electrical

(4) 4.5 watt integrated LED lamp = 18W total. 120V 60 Hz AC operation. Dimmable with standard 2-wire dimmers.

Lamping

Unit is supplied with rail heads. Each rail head contains high power LEDs which produce a total of 200+ lumens per head. The LEDs have an average life of 35,000 hours. 3000K.

Certification

All fixtures are cETLus listed for damp locations. ENERGY STAR qualified.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 3 years from date of purchase.

Specifications and dimensions
subject to change without notice.

Ordering Information:

Satin Nickel	Rubbed Bronze	Qty.	Lumens	L	W	H
TRRF4200LEDSN3K	TRRF4200LEDRB3K	4 Heads	200+ lm/head	36-5/8"	5-1/4"	8"

Wall Dimmer Compatibility Chart

Product can be dimmed to 10% of full scale using a standard two-wire dimmer.

Brand	Model #
Leviton®	6633, 6681, 6621-WWP, 6631-WWP
Lutron®	TG-600P, TG-603P, LG-600H
Legrand®/Pass & Seymour	T600WV, WS700TCCCVG

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

