


ESTATE® PRESSURE BALANCE BATH/SHOWER FITTING



T722.502 Bath/Shower Trim Shown

GENERAL DESCRIPTION:

SHOWERHEAD

3-function 7-1/16" showerhead. At maximum 2.5 gpm/9.5 L/min. flow rate.

WALL TUB SPOUT

Metal slip-on diverter spout.

WALL VALVE TRIM

Metal lever handle. Metal wall escutcheon.


- Coordinates with Estate® Suite of fixtures.
- Available Exclusively at Ferguson® Showrooms.

MODEL NUMBER:

TRIM KITS:

- □ T722.502 Estate BATH/SHOWER Trim Kit Metal lever handle. LESS valve body.
- □ T722.501 Estate SHOWER ONLY Trim Kit Metal lever handle. LESS valve body.
- □ T722.500 Estate VALVE ONLY Trim Kit Metal lever handle. LESS valve body.

For use with R110 Series Pressure Balance Valves. See reverse side for available Rough Valves.



SUGGESTED SPECIFICATION


Bath/shower fitting shall feature 3-functionaa showerhead with Max. 2.5 gpm/9.5 L/min. flow rate. Fitting shall be: American Standard - Trim Kit Model # T722.50_.___ and Valve Body Model # R11_.



CODES AND STANDARDS

These products meet or exceed the following codes and standards:

ANSI A117.1 ASSE 1016 ASME A112.18.1 / CSA B125.1



		* TRIM & ROUGH MUST BE ORDERED SEPARATELY.	Finish Options			
TRIM KITS *	Product		Polished Chrome	PVD Polished Nickel	Legacy Bronze	PVD Satin Nickel
	Number	Description	002	013	278	295
	T722.502	Bath/Shower Trim Kit. Metal lever handle. Showerhead. LESS valve body.				
	T722.501	Shower Only Trim Kit. Metal lever handle. Showerhead. LESS valve body.				
	T722.500	Valve Trim Only. Metal lever handle. LESS valve body.				

	Product Number	Description
ROUGH VALVE BODIES	R111	Rough Valve Body less trim. Universal inlets/outlets.
	R111SS	Rough Valve Body less trim. Universal inlets/outlets with Screwdriver Stops.
	R110	Rough Valve Body less trim. Direct sweat inlets/outlets.
	R110SS	Rough Valve Body less trim. Direct sweat inlets/outlets with Screwdriver Stops.
	R115	Rough Valve Body less trim. Female Thread inlets/outlets.
	R115SS	Rough Valve Body less trim. Female Thread inlets/outlets with Screwdriver Stops.
	R117	Rough Valve Body less trim. PEX inlets/universal outlets for Crimp Ring PEX system (ASTM F1807).
	R117SS	Rough Valve Body less trim. PEX inlets/universal outlets for Crimp Ring PEX system (ASTM F1807) with Screwdriver Stops.
	R118	Rough Valve Body less trim. PEX inlets/universal outlets for Cold Expansion PEX system (ASTM F1960).
	R118SS	Rough Valve Body less trim. PEX inlets/universal outlets for Cold Expansion PEX system (ASTM F1960) with Screwdriver Stops.
	R119	Rough Valve Body less trim. CPVC inlets/universal outlets.
	R119SS	Rough Valve Body less trim. CPVC inlets/universal outlets with Screwdriver Stops.



Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for the physically challenged.