

LANDFAIR[®] BRIDGE LAVATORY FAUCET



- Cast brass spout and side valves
- Ceramic disc valve cartridges
- White porcelain and metal index buttons included
- Non-swivel spout
- Decorative center drain activator and Speed Connect® with 1-1/4" drain
- Lead Free—faucet contains ≤0.25% total lead content by weighted volume
- Maximum flow rate: 1.5 gpm (5.7 L/min)
- Low flow rate: 1.2 gpm (4.5 L/min)

CODES AND STANDARDS

Meets or Exceeds ASME A112.18.1/ CSA B125.1/NSF 61/Section 9

EPA WaterSense® High Efficiency Lavatory Faucet Specification

Certified Compliant with 0.25% Weighted Average Lead Content Regulations

Αναι	ABLE	FINISH	=S

Polished Chrome Carbon Bronze Brushed Nickel Platinum Nickel



150


DESCRIPTIONPRODUCT NUMBER1.5 gpm (5.7 L/min)D35107254.XXXBridge Lavatory FaucetD35107254.XXX1.2 gpm (4.5 L/min)D3510725C.XXXBridge Lavatory FaucetD3510725C.XXX



ROUGH-IN DIAGRAM SHOWN ON NEXT PAGE



LANDFAIR[®] BRIDGE LAVATORY FAUCET



IMPORTANT: These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.