# Figure ABFBK PIPING PRODUCTS



# AQUATHERM BUTTERFLY FLANGE BOLT KIT

#### **Features**

- For 150# ANSI Flanges
- · Lengths for Joining to Butterfly Flange
- Material: Carbon SteelFinish: Zinc Plated
- \*Sizes: 2" to 24"

#### **Standards**

- · Bolts:
  - o Material ASTM A307A Grade A
  - Dimensions ASME B18.2.1
  - o Thread Class 2A
- Nuts:
  - o Material SAE J995 Grade 2
  - o Dimensions ASME B18.2.2
  - o Thread Class 2B
- · Washers:
  - o ASME B18.22.1

## **Bolt Properties**

Tensile: 60 KSI Minimum
Elongation: 18% Minimum
Hardness: 69 - 100 Rb

\* Based on 1/16" raised face and 1/8" gasket



### **Figure Number Matrix**

FNW A	BF	BK	Siz	e	
_A_	ь ВЕ	BK_	SIZE CODE		
Aquatherm	Butterfly	Bolt Kit	1/2 = D	6 = U	
			3/4 = F	8 = X	
			1 = G	10 = 10	
			1-1/4 = H	12 = 12	
			1-1/2 = J	14 = 14	
			2 = K	16 = 16	
			2-1/2 = L	18 = 18	
			3 = M	20 = 20	
Nata CDD. (			4 = P	24 = 24	
Note SDR: 6	o ocup		5 = S		
I				I	

Pack Quantities & Bolt Sizes (inches)

Size	Bolt Qty	Nut Qty	Washer Qty	Diameter	Bolt Length	SDR Bolt Length	Weight
2	8	8	8	5/8	2		1.10
2-1/2	8	8	8	5/8	2		1.10
3	8	8	8	5/8	2		1.10
4	16	16	16	5/8	2-1/4		2.35
6	16	16	16	3/4	3		4.32
8	16	16	16	3/4	3-1/4		4.55
10	24	24	24	7/8	3-1/2		10.38
12	24	24	24	7/8	4-3/4		12.69
-	-	-	-	-	-	4	11.30
14	24	24	24	1	5-1/2		19.01
-	-	-	-	-	-	4-1/4	16.00
16	32	32	32	1	4-3/4		22.94
-	-	-	-	-	-	4	20.53
18	32	32	32	1-1/8	6		35.41
-	-	-	-	-	-	5	31.34
20	40	40	40	1-1/8	5		39.17
24	40	40	40	1-1/8	5		39.17

DOC: FNWABFBK Ver. 4/2016

© 2016 - FNW. All rights reserved.

The FNW logo is a trademark of Ferguson Enterprises, Inc., PL Sourcing, PO Box 2778, Newport News, VA 23609

www.fnw.com