## Figure ABKFAFA PIPING PRODUCTS



# AQUATHERM FLANGE ADAPTER TO FLANGE ADAPTER BOLT KIT

#### **Features**

- For 150# ANSI Flanges
- Lengths for Joining Flange Adapter to Flange Adapter
- Material: Carbon SteelFinish: Zinc Plated
- \*Sizes: 1" to 24"

#### **Standards**

- · Bolts:
  - o Material ASTM A307A Grade A
  - Dimensions ASME B18.2.1
  - o Thread Class 2A
- Nuts:
  - o Material SAE J995 Grade 2
  - o Dimensions ASME B18.2.2
  - o Thread Class 2B
- · Washers:
  - o ASME B18.22.1

#### **Bolt Properties**

Tensile: 60 KSI Minimum
Elongation: 18% Minimum
Hardness: 69 - 100 Rb

### /2" and 22" Figure Number Matrix Pack Quantities & Bolt Sizes (inches)

FNW A	ВК	FA FA	Size	
_A_	BK	FLANGE ADAPT	ER <u>SIZE C</u>	DDE
Aquatherm	Bolt Kit	Flange Adapter	1/2 = D 3/4 = F	6 = U 8 = X
			1 = G	10 = 10
			1-1/4 = H 1-1/2 = J	12 = 12 14 = 14
			2 = K 2-1/2 = L	16 = 16
			3 = M	18 = 18 20 = 20
Note SDR: (	6" & up		4 = P 5 = S	22 = 22 24 = 24
				24 - 24

OIZE	DOIL GLY	Hut Gty	washer dry	Diameter	Doit Length	ODIN DOIL Length	weight
1	4	4	4	1/2	3-1/2		0.48
1-1/4	4	4	4	1/2	3-1/2		0.48
1-1/2	4	4	4	1/2	3-1/2		0.48
2	4	4	4	5/8	4		0.86
2-1/2	4	4	4	5/8	4-1/2		0.90
3	4	4	4	5/8	4-1/2		0.90
3-1/2	8	8	8	5/8	4-1/2		1.80
4	8	8	8	5/8	4		1.72
6	8	8	8	3/4	6		3.52
-	-	-	-	-	*	5-1/2	3.29
8	8	8	8	3/4	6-1/2		3.85
-	-	-	-	-	*	6	3.52
10	12	12	12	7/8	8-1/2		8.42
-	-	-	-	-	*	6-1/2	8.19
12	12	12	12	7/8	8-1/2		9.57
-	-	-	-	-	*	8	9.11
-	-	-	-	-	*	6-1/2	8.19
14	12	12	12	1	10		15.22
-	-	-	-	-	*	8-1/2	13.42
-	-	-	-	-	*	7-1/2	11.91
16	16	16	16	1	9		18.29
-	-	-	-	-	*	8	16.28
18	16	16	16	1-1/8	10		26.35
-	-	-	-	-	*	8-1/2	22.28

DOC: FNWABKFAFA Ver. 4/2016

© 2016 - FNW. All rights reserved.

The FNW logo is a trademark of Ferguson Enterprises, Inc., PL Sourcing, PO Box 2778, Newport News, VA 23609

www.fnw.com

<sup>\*</sup> Based on 1/16" raised face and 1/8" gasket

<sup>\*</sup> Excluding 3-1/2" and 22"