

# Composed™ Single-handle Sink Faucet K-73167-4

### **Features**

- Metal construction.
- ADA Compliant Lever handle .
- Leak free ceramic disc valve allows both volume and temperature control.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- High-temperature limit setting for added safety.
- Single-hole mounting.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Complete range of faucets, accessories and showering components to coordinate a full bathroom.
- 1.2 gal/min (4.5 l/min) maximum flow rate [max at 60 psi (4.1 bar)]
- Not compatible with lavatories with centerset drillings.





## Codes/Standards

ASME A112.18.1/CSA B125.1

NSF 61

**ADA** 

NSF 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

# KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

Color tiles intended for reference only.

Color Code Description

CP Polished Chrome


TT Vibrant Titanium





# Composed™

Single-handle Sink Faucet K-73167-4



## **Technical Information**

All product dimensions are nominal.

Valve body: Cast Brass

Drain with overflow: YES
Drain tailpiece YES

included: **Spout:** 

Spout reach: 5-15/16" (151 mm) Handle clearance: 1-9/16" (40 mm)

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

#### **Notes**

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

