

Highline® Comfort Height® Two-Piece Toilet K-5481-RA

Features

- Vitreous china.
- Comfort Height® Round-front bowl.
- Class Five® flushing system.
- Includes right-hand polished chrome trip lever.
- 1.28 gpf (4.8 lpf).
- 2-1/8" (54 mm) fully glazed trapway.
- 12" (305 mm) rough-in.
- Less seat and supply line.
- 10-1/2" (267 mm) x 8-1/4" (210 mm) water area.
- 27-3/4" (705 mm) x 18" (457 mm) x 31-1/4" (794 mm).
- Floor mount / Floor outlet.

Optional Accessories

K-4639 Toilet Seat K-7637 Angle Supply with Stop (single)

Components

Product includes:

K-5393 Comfort Height® Round-Front Bowl K-4467-RA Toilet Tank Additional included component/s: Tank cover, Trip lever, and Bolt cap accessory pack.





Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC)

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Descriptio
	0	White
	96	Biscuit
	47	Almond





Highline®

Comfort Height® Two-Piece Toilet K-5481-RA



Technical Information

All product dimensions are nominal.

Toilet type: Two-piece, Floor-mount

Waste Outlet: Floor

Bowl shape: Round front Flush type: Class Five Trap passageway: 2-1/8" (54 mm)

Water Consumption

Full: 1.28 gpf (4.8 lpf)

Water surface size: 10-1/2" x 8-1/4" (267 mm x 210 mm)

Rim to water surface: 5-3/8" (137 mm)
Rough-in: 12" (305 mm)
Seat-mounting holes: 5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.

