

### Features

- Vitreous china.
- Comfort Height® Round-front bowl.
- AquaPiston® flushing system.
- Includes left-hand polished chrome trip lever.
- 1.28 gpf (4.8 lpf).
- 2-1/8" (54 mm) fully glazed trapway.
- 12" (305 mm) rough-in.
- Less seat and supply.
- 11-1/2" (292 mm) x 8-3/4" (222 mm) water area.
- 28-3/8" (721 mm) x 17-13/16" (452 mm) x 31-1/2" (800 mm).
- Floor mount / Floor outlet.

### Optional Accessories

K-1954 Touchless Toilet Flush Kit  
 K-4009 Toilet Seat  
 K-4639 Toilet Seat  
 K-4644 Toilet Seat  
 K-4662 Toilet Seat  
 K-4663 Toilet Seat  
 K-4689 Toilet Seat  
 K-4695 Toilet Seat  
 K-4775 Toilet Seat  
 K-4816 Toilet Seat  
 K-5589 Round-Front Toilet Seat  
 K-5639 Round-Front Toilet Seat  
 K-7637 Angle Supply with Stop (single)  
 K-7671 Toilet Seat  
 K-7673 Round-Front Toilet Seat  
 K-4686-A Toilet Seat  
 K-4716-T Toilet Seat  
 K-9167-L Trip Lever

### Components

Product includes:

K-4387 Round-Front Bowl  
 K-4433 1.28 gpf Tank

Additional included component/s: Tank cover, Trip lever, Bolt cap accessory pack, and Tank accessory pack.



### Codes/Standards








ASME A112.19.2/CSA B45.1  
 DOE - Energy Policy Act 1992  
 EPA WaterSense®


### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Color/Finishes

*Color tiles intended for reference only.*

| Color  | Code | Description  |
|--|------|--------------|
|  | 0    | White        |
|  | 96   | Biscuit      |
|  | 47   | Almond       |
|  | NY   | Dune         |
|  | 95   | Ice™ Grey    |
|  | G9   | Sandbar      |
|  | 7    | Black Black™ |



## Technical Information

All product dimensions are nominal.

Toilet type: Two-piece, Floor-mount

Waste Outlet: Floor

Bowl shape: Round front

Flush type: AquaPiston

Trap passageway: 2-1/8" (54 mm)

Water Consumption

Full: 1.28 gpf (4.8 lpf)

Water surface size: 11-1/2" x 8-3/4" (292 mm x 222 mm)

Rim to water surface: 6-1/8" (156 mm)

Rough-in: 12" (305 mm)

Seat-mounting holes: 5-1/2" (140 mm)

## Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.