

Features

- Vitreous china.
- Comfort Height® Round-front bowl.
- AquaPiston® flushing system.
- Includes right-hand polished chrome trip lever.
- 1.28 gpf (4.8 lpf).
- 2-1/8" (54 mm) fully glazed trapway.
- 12" (305 mm) rough-in.
- Less seat and supply.
- 11-1/2" (292 mm) x 8-3/4" (222 mm) water area.
- 28-3/8" (721 mm) x 18-7/8" (479 mm) x 31-1/8" (790 mm).
- Floor mount / Floot outlet.

Optional Accessories

K-1954 Touchless Toilet Flush Kit
 K-4009 Toilet Seat
 K-4639 Toilet Seat
 K-4644 Toilet Seat
 K-4662 Toilet Seat
 K-4663 Toilet Seat
 K-4689 Toilet Seat
 K-4695 Toilet Seat
 K-4775 Toilet Seat
 K-4816 Toilet Seat
 K-5589 Round-Front Toilet Seat
 K-5639 Round-Front Toilet Seat
 K-7637 Angle Supply with Stop (single)
 K-7671 Toilet Seat
 K-7673 Round-Front Toilet Seat
 K-4716-T Toilet Seat
 K-9167-R Trip Lever

Components

Product includes:

K-4387 Round-Front Bowl
 K-4434-RA Toilet Tank

Additional included component/s: Tank cover, Trip lever, Bolt cap accessory pack, and Tank accessory pack.



Codes/Standards




ASME A112.19.2/CSA B45.1
 DOE - Energy Policy Act 1992
 EPA WaterSense®
 California Energy Commission (CEC)



KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond



Seat-mounting holes: 5-1/2" (140 mm)

For back-to-back toilet installations: Use only a 45° double wye fitting.