



# Cimarron® Comfort Height® Toilet K-3888-RA

## Features

- Vitreous china.
- Comfort Height® round-front bowl.
- AquaPiston® flushing system.
- Includes right-hand polished chrome trip lever.
- 1.6 gpf (6.0 lpf).
- 2-1/8" (54 mm) fully glazed trapway.
- 12" (305 mm) rough-in.
- Less seat and supply.
- 11" (279 mm) x 8-3/4" (222 mm) water area.
- 27-1/4" (692 mm) x 17-5/8" (448 mm) x 30-1/2" (775 mm).
- Floor mount / Floor outlet.

## Optional Accessories

K-9466-R Right-hand Trip Lever  
K-9470-R Right-hand Trip Lever  
K-1954 Touchless Toilet Flush Kit  
K-4009 Toilet Seat  
K-4639 Toilet Seat  
K-4644 Toilet Seat  
K-4662 Toilet Seat  
K-4663 Toilet Seat  
K-4689 Toilet Seat  
K-4695 Toilet Seat  
K-4775 Toilet Seat  
K-4816 Toilet Seat  
K-5589 Round-Front Toilet Seat  
K-5639 Round-Front Toilet Seat  
K-7637 Angle Supply with Stop (single)  
K-4686-A Toilet Seat  
K-4716-T Toilet Seat

## Components

Product includes:

K-4347 Comfort Height® Round-front Bowl  
K-4167-RA Toilet Tank

Additional included component/s: Tank cover, Trip lever, Bolt cap accessory pack, and Tank accessory pack.



## Codes/Standards




ASME A112.19.2/CSA B45.1  
DOE - Energy Policy Act 1992  
California Energy Commission (CEC)


## KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

## Available Color/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond



## Technical Information

All product dimensions are nominal.

Toilet type:	Two-piece, Floor-mount
Waste Outlet:	Floor
Bowl shape:	Round front
Flush type:	AquaPiston
Trap passageway:	2-1/8" (54 mm)
Water Consumption	
Full:	1.6 gpf (6 lpf)
Water surface size:	11" x 8-3/4" (279 mm x 222 mm)
Rim to water surface:	5-1/4" (133 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

## Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.