



Persuade® Curv

Dual Flush Toilet

K-3723

Features

- Vitreous china
- Two-piece toilet
- Comfort Height® Elongated bowl
- Dual Flush flushing system
- Includes top-mount dual flush trip lever
- 1.6 gpf (6.0 lpf) or 1.0 gpf (3.8 lpf)
- Fully skirted trapway
- 12" (305 mm) rough-in
- Supply line included
- 4-1/2" (114 mm) x 5-3/4" (146 mm) water area
- 28-5/8" (727 mm) x 14-3/16" (360 mm) x 32-1/2" (826 mm)
- Floor mount / Floor outlet

Optional Accessories

K-4650 Toilet Seat
K-186 Dual Flush Actuator
K-4008 Toilet Seat
K-4636 Toilet Seat
K-4652 Toilet Seat
K-4659 Toilet Seat
K-4684 Toilet Seat
K-4688 Toilet Seat
K-4694 Toilet Seat
K-4709 Toilet Seat with Cleansing Functionality
K-4737 Toilet Seat with Cleansing Functionality
K-4748 Toilet Seat
K-4774 Toilet Seat
K-4814 Toilet Seat
K-4888 Elongated Toilet Seat
K-5588 Elongated Toilet Seat
K-5638 Elongated Toilet Seat
K-7637 Angle Supply with Stop (single)
K-7659 Angle Stop
K-7668 Straight Stop
K-9384 Dual-flush Actuator
K-4761-BN Toilet Seat
K-4761-CP Toilet Seat

Components

Product includes:

K-4353 Toilet Bowl
K-4441 Toilet Tank

Additional included component/s: Tank cover, Dual flush push buttons, Installation kit, Installation template, and Tank accessory pack.



Codes/Standards







ASME A112.19.2/CSA B45.1
ASME A112.19.14
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	95	Ice™ Grey
	7	Black Black™



USA/Canada: 1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

6-15-2017 09:26

THE BOLD LOOK
OF **KOHLER**®



Technical Information

All product dimensions are nominal.

Toilet type: Two-piece, Floor-mount

Waste Outlet: Floor

Bowl shape: Elongated front

Trap passageway: 2" (51 mm)

Water Consumption

Full: 1.6 gpf (6 lpf)

Reduced: 1 gpf (3.8 lpf)

Water surface size: 4-1/2" x 5-3/4" (114 mm x 146 mm)

Rim to water surface: 8-1/2" (216 mm)

Rough-in: 12" (305 mm)

Seat-mounting holes: 5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.

IMPORTANT! The rough-in must be 12" (305 mm) or more from the base of the wall or baseboard. Install or relocate the supply and outlet as necessary to conform to rough-in dimensions.

If this toilet is installed in new construction, install a new supply stop following the dimensions in the diagram.

In installations with the supply stop installed, the existing supply stop may need to be relocated if it is less than 8-1/2" (216 mm) from the centerline of the toilet. Dry fit the toilet to confirm if the supply stop needs to be relocated.

The supplied hose will extend roughly 6" (152 mm) from the toilet. If the supplied hose does not reach the supply stop, a longer supply hose may be used.

For back-to-back toilet installations: Use only a 45° double wye fitting.