# **KOHLER**<sub>®</sub>

#### Features

- Includes cutout templates.
- 9-inch depth.
- Includes 1 sink rack.

#### Material

• KOHLER Neoroc material.

#### Installation

- Includes 1 faucet hole on rear deck (3 more faucet holes available for knockout with ball-peen hammer & punch.
- 36-inch minimum base cabinet width for under-mount installation.
- 36-inch minimum base cabinet width for top-mount installation.
- Top-mount or under-mount installation.
- Strainer not included.

#### **Recommended Accessories**

K-9000 P-Trap K-8801 Sink Strainer K-8799 Sink Strainer

#### **Optional Accessories**

K-5186 Right-Bowl Sink Rack

#### Components

Additional included component/s: K-5662.



### Codes/Standards

CSA B45.5/IAPMO Z124

# KOHLER<sup>®</sup> Neoroc<sup>®</sup> Sinks Lifetime Limited Warranty

See website for detailed warranty information.

### Available Color/Finishes

Color tiles intended for reference only.

Color Code Description



CM1 Neoroc® Matte Black

CM2 Neoroc® Matte Brown




Kennon®

Top-/Under-Mount Kitchen Sink K-8185-1



## Kennon® Top-/Under-Mount Kitchen Sink K-8185-1



#### **Technical Information**

All product dimensions are nominal.	
Installation:	Under-mount, Top-mount
Min. base cabinet width:	36" (914 mm)
Bowl area (Left): Bowl area:	Length: 14-9/16" (370 mm) Width: 16-13/16" (427 mm) Bowl depth: 9" (229 mm) Water depth: 9" (229 mm) Length: 14-9/16" (370 mm) Width: 16-13/16" (427 mm) Bowl depth: 9" (229 mm)
Drain hole: Template:	Water depth: 9" (229 mm) 3-7/8" (98 mm) 1281758-7, required, included

#### Notes

Install this product according to the installation instructions.