



FEATURES

- Energy Savings of up to 90%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Frosted Ribbed Glass with Aluminum Construction in Black Finish
- Die Formed Aluminum
- Replaces 60W Incandescent

OPTICS

- Frosted Ribbed Glass

APPLICATIONS

- Hallways
- Corridors
- Outdoor Wall

CERTIFICATIONS

- UL/cUL Listed for Wet Locations
- Energy Star
- Lighting Facts

SPECIFICATIONS

Part Number: **LED8822-05**

Manufacturer Limited Warranty: 3 Years

Kelvin Temperature (CCT): 3000K

Wattage: 6 W

Lumens: 440 lm

Efficacy: 73.33 lm/w

CRI: 70

Dimmable: No

Input Voltage: DC 120V

Certifications: UL Listed

DLC Listed: No

Average Hour Life: 50,000 hrs

Max. Ambient Temperature: 45°C

Min. Ambient Temperature: -20°C

Power Factor: >0.9

THD: <20%

TECHNICAL

Weight: 1.98 lbs

Length: 5.8

Product Height: 8.4"

Product Width: 4.6"


LED Beam Angel: 120

LED Type: Integrated LED Array





LINE DRAWINGS



LIGHTING FACTS

LED lighting facts®
A Program of the U.S. DOE

Light Output (Lumens) **440**
Watts **6**
Lumens per Watt (Efficacy) **73.33**

Color Accuracy
Color Rendering Index (CRI) **70**

Light Color
Correlated Color Temperature (CCT) **3000 (Bright White)**

2700K 3000K 4500K 6500K

Warm White Bright White Daylight

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: ZMBK-VGWTAP (Revised)
Model Number: LED8822-05
Type: Luminaire - Decorative