



### FEATURES

- Energy Savings of up to 90%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Aluminum Construction in Black Finish
- Die Formed Aluminum
- Replaces 60W Incandescent

### **OPTICS**

Clear Glass

## **APPLICATIONS**

Outdoor Wall

## **CERTIFICATIONS**

- UL/cUL Listed
- Energy Star
- Lighting Facts

SPECIFICATIONS			
Part Number: LED7002-05			
Limited Manufacturer Warranty:	3 Years	Certifications:	UL Listed
Kelvin Temperature (CCT):	3000K	DLC Listed:	No
Wattage:	6 W	Average Hour Life:	50,000 hrs
Lumens:	460 lm	Max. Amblent Temperature:	45°C
Efficacy:	76.67 lm/w	Min. Amblent Temperature:	-20°C
CRI:	70	Power Factor:	>0.9
Dimmable:	No	THD:	<20%
Input Voltage:	DC 120V		
TECHNICAL			
Weight:	1.59 lbs	Product Width:	4-5/8'
Length:	5-3/4"	LED Beam Angel:	120
Product Height:	83/8"	LED Type:	Integrated LED Array









Cordelia Lighting Main (800) 345-0542

# SFERGUSON

# LINE DRAWINGS





### ED lighting facts® Cordelia Lighting LED 0 460 Light Output (Lumens) Watts 6 Lumens per Watt (Efficacy) 76.67 Color Accuracy Color Rendering Index (CRI) 70 Light Color 3000 (Bright White) nperature (CCT) Warm White Bright White Daylight 6500K 2700K 3000K 4500K All results are according to IESNA LM-79-2008: Approved Method for the Electrical and

LIGHTING FACTS

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: ZMBK-PYEIBO (Revised ) Model Number: LED7002-05 Type: Luminaire - Decorative

