

# Highcliff™ Ultra

Elongated Floor Mount Flushometer Bowl K-96058

#### **Features**

- Elongated bowl, ADA compliant.
- 1-1/2" rear spud.
- 10" x 7" water surface size.
- Also available with antimicrobial finish K-96058-SS.
- Glazed 2-1/8" trapway.

#### Material

Vitreous china.

## **Technology**

- Designed to outperform competitors in bowl cleanliness and plug resistance.
- Maximum waste removal.
- Engineered for toilet seat cover removal.
- Excellent bowl rinse.
- Engineered to flush effectively in buildings with low supply pressure and flow\*.
- Maximum drain line carry at all flush volumes per ASME Standard.

#### Installation

- 26-3/8" L x 14-5/8" W x 16-7/8" H
- 11" rough-in.
- Replaces Highcrest K-4301 and Highcliff K-4367. Height and footprint may vary.

## **Water Conservation & Rebates**

- 1.28 to 1.6 gpf flush range (1.28 and 1.6 gpf).
- WaterSense compliant when used with a 1.28 gpf WaterSense flushometer.

#### Components

Additional included component/s: Spud, and Bolt Cap Accessory Pack.





ADA CSA B651

B651 ∥ OBC

## Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

## **KOHLER® One-Year Limited Warranty**

See website for detailed warranty information.

### **Available Color/Finishes**

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
413	7	Black Black™





## Highcliff™ Ultra

Elongated Floor Mount Flushometer Bowl K-96058



### **Technical Information**

All product dimensions are nominal.

Toilet type: Flushometer, Floor-mount

Waste Outlet: Floor

Bowl shape: Elongated front

Flush type: Flushometer valve siphon

Spud size: 1-1/2", Inlet, Top Trap passageway: 2-1/8" (54 mm)

Water Consumption

Full: 1.28 gpf (4.8 lpf) or 1.6 gpf (6 lpf) Water surface size: 10" x 7" (254 mm x 178 mm)

Rim to water surface: 6" (152 mm)
Rough-in: 11" (279 mm)
Seat-mounting holes: 5-1/2" (140 mm)

## **Fixture Supply Requirements**

Min static pressure: 35 psi (241.3 kPa)
Max static pressure: 80 psi (551.6 kPa)
Min flowing pressure: 25 psi (172.4 kPa)
Min flow rate: 25 gpm (94.6 lpm)

#### **Notes**

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.

Requires flushometer valve to match desired water consumption 1.28 gpf (4.8 lpf) or 1.6 gpf (6 lpf).

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Plumbing Codes require elongated toilets and elongated, open-front toilet seats in public bathrooms.

Accessibility standards require controls to be located on the open side of the toilet.

