

# FEATURES

- Energy Savings of up to 87% •
- Lumen Maintenance over 70% @ 50,000+ Hours .

SFERGUSON®

- No UV/IR Radiation, No Toxic Mercury .
- Steel Clips in Brushed Nickel and Oil Rubbed Bronze Finish
- Die Formed of 22 Gauge Plated Steel
- Replaces 2 x 60W Incandescent •

### **OPTICS**

• Alabaster-Style Glass

## **APPLICATIONS**

- Hallways
- Bedrooms
- Lobbies
- Corridors

## **CERTIFICATIONS**

- UL/cUL Listed
- **Energy Star**
- **Lighting Facts**

### SPECIFICATIONS

| Part Number: LED15007B         |               |                           |                      |
|--------------------------------|---------------|---------------------------|----------------------|
| Manufacturer Limited Warranty: | 3 Years       | Certifications:           | UL Listed            |
| Kelvin Temperature (CCT):      | 2700K         | DLC Listed:               | No                   |
| Wattage:                       | 15.3W         | Average Hour Life:        | 50,000 hrs           |
| Lumens:                        | 1397 lm       | Max. Ambient Temperature: | 45°C                 |
| Efficacy:                      | 91.31 lm/w    | Min. Ambient Temperature: | -20°C                |
| CRI:                           | 80            | Power Factor:             | >0.9                 |
| Dimmable:                      | 0-10V Dimming | THD:                      | <20%                 |
| Input Voltage:                 | DC 120V       |                           |                      |
| TECHNICAL                      |               |                           |                      |
| Weight:                        | 5.31 lbs      | Product Width:            | 16-1/4"              |
| Length:                        | 16-1/4"       | LED Beam Angel:           | 120                  |
| Product Height:                | 4-1/2"        | LED Type:                 | Integrated LED Array |









tina acts

# **FACILITIES SUPPLY**

# LINE DRAWINGS





# LIGHTING FACTS

| Lighting facts   | Cordelia Lightin<br>S®<br>JOE |
|--|-------------------------------|
| Light Output (Lumens)<br>Watts<br>Lumens per Watt (Efficacy) | 1397<br>15.3<br>91.31         |
| Color Accuracy<br>Color Rendering Index (CRI)                | 81                            |
| Light Color<br>Correlated Color Temperature (CCT) 2700 (V    | Warm White)                   |
| Warm White Bright White<br>2700K 3000K 4500K                 | Daylight<br>6500K             |

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

### Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: ZMBK-5NYUU4 (1/17/2017) Model Number: LED15007B Type: Luminaire - Downlight