

<b>N</b>	<div style="display: flex; justify-content: space-between; align-items: center;"> <div style="text-align: left;"> <b>SMITH® JAY R. SMITH MFG. CO.®</b>  <small>MEMBER OF MORRIS GROUP INTERNATIONAL  POST OFFICE BOX 3237  MONTGOMERY, ALABAMA 36109-0237 (USA)  TEL: 334-277-8520 FAX: 888-377-7818 www.jrsmith.com</small> </div> <div style="text-align: center;">   <small>MEMBER OF:</small> </div> <div style="text-align: center;">   <small>MEMBER OF:</small> </div> </div>				<b>LOCATION</b>			
	<h2 style="margin: 0;">FINISHED FLOOR CLEANOUTS WITH "TWIS-TO-FLOOR®" ADJUSTABLE TOPS</h2>							
DRAWING NUMBER <b>S4031</b>	SIZE <b>A</b>	SCALE: <b>NONE</b>	DATE: <b>2-16-70</b>	APPROVED BY: <b>JM</b>	CHECKED BY: <b>BH</b>	DRAWN BY: <b>RK</b>	DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCE AND CHANGE WITHOUT NOTICE	
<div style="text-align: center; border-bottom: 2px solid black; margin-bottom: 10px;"> <b>ROUND NICKEL BRONZE TOP</b> </div> <p><b>FUNCTION:</b> For use in finished floors bearing foot and medium load wheeled traffic. Allows for easy floor level adjustment.</p> <p>"C.O." cast in Secured Cover</p> <div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;"> <p style="margin-top: 10px;"><b>TWIS-TO-FLOOR® ADJUSTMENT</b></p> <p><b>SPEEDI-SET OUTLET ▲</b></p> <p>"A" (Pipe Size) = 02(50), 03(75) or 04(100)</p> </div> <div style="text-align: left; margin-top: 20px;"> <p><b>* This Dimension to Internal Stop of Speedi-set Gasket.</b></p> <p><b>NOTE:</b> For applications using core drilling, the largest diameter of the cleanout assembly is 6 5/16"(160).</p> </div> </div> <div style="display: flex; justify-content: space-between; margin-top: 20px;"> <div style="width: 45%;"> <p><input type="checkbox"/> Fig. 4031L.....Gasket Seal - ABS Plug</p> <p><input type="checkbox"/> Fig. 4032L.....Gasket Seal - Bronze Plug</p> <p><input type="checkbox"/> Fig. 4033L.....Taper Thread - Bronze Plug</p> <p><input type="checkbox"/> Fig. 4034L.....Taper Thread - ABS Plug</p> </div> <div style="width: 50%;"> <p>(Twis-to-Floor® design shown with gasketed plug.)</p> <p><b>NOTE:</b> Dimensions shown in parentheses are in millimeters.</p> </div> </div> <div style="display: flex; justify-content: space-between; margin-top: 20px;"> <div style="width: 30%;"> <p><b>REGULARLY FURNISHED:</b></p> <p>Duco Cast Iron Cleanout with Round Adjustable Scoriated Secured Nickel Bronze Top. Closure Plug Type as Indicated By Figure Number Selected.</p> <p>▲ Available in Extra Heavy, Service Weight or NO-HUB.</p> </div> <div style="width: 35%;"> <p><b>VARIATIONS:</b></p> <p><input type="checkbox"/> Flashing Flange -F</p> <p><input type="checkbox"/> Flange with Flashing Clamp -F-C</p> <p><input type="checkbox"/> Carpet Clamping Type -X</p> <p><input type="checkbox"/> Carpet Marker Type -Y</p> <p><input type="checkbox"/> Vandal Proof Top -U</p> <p><input type="checkbox"/> Wide Flange (DX)</p> </div> <div style="width: 30%;"> <p><b>OPTIONAL MATERIALS:</b></p> <p><input type="checkbox"/> Galvanized Cast Iron -G</p> <p><input type="checkbox"/> Polished Bronze Top -PB</p> </div> </div>								
FIGURE NUMBER <b>4031 SERIES</b>	N M L K	11-15-19 12-18-08 12/17/04 07/26/02	Revised Variations Revised Variations Added Core-Drilling Note Corrected Clamp & Flange view	TBW RN JJ JJ	CL BW CL CL	WEIGHT POUNDS	VOLUME CUBIC FEET	FIGURE NUMBER <b>4031 SERIES</b>
REV.	DATE	DESCRIPTION			BY	CKD. BY		



**WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov