


TAG:

# Service Sink Faucet

#### Architect/Engineering Specifications:

8" wall mount mixing faucet with polished chrome plated brass body, polished chrome plated brass spout with vacuum breaker, pail hook and garden hose male outlet, compression cartridges with spring checks, lever handles, 1/2" NPT female extension inlets, built-in service stops in body, and lower support rod. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9, NSF 372 and ASSE 1001. Meets ADA ANSI/ICC A117.1 requirements.



#### Features & Benefits:

- 8" wall mount mixing faucet with polished chrome plated brass body
- Spout with vacuum breaker, pail hook & 3/4" darden hose male outlet
- Lever handles with color coded indexes
- Quarter-turn Eterna compression cartridges with spring checks to prevent cross flow of water
- 1/2" NPT eccentric female inlets w/ Ø2" flanges & 4" extensions
- Adjustable centers from 7 3/4" to 8 1/4"
- Built-in service stops
- Lower support rod
- Material: Polished chrome plated brass body & spout and chrome plated metal handles

## **Optional Handles & Optional Cartridges**

#### **Optional Handles**

## **Optional Cartridges With Checks**

□ 4" Wrist Action □ Lever (Standard) □ 4-Arm

□ Quarter Turn Cerama w/ Check Valve

□ Quarter Turn Eterna w/ Spring Check (Standard)

# **Product Compliance:**

- ASME A112.18.1 / CSA B125.1
- NSF 61-Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)
- ASSE 1001 (VB)

Warranty: One Year (Limited)

#### Performance Data:

- Pressure: 20 125 psi
- Temperature: 40 °F 140 °F
- Flow Rate: 12.96 GPM @ 60 psi











