

Panel Flange with Hose Cock


Architect/Engineering Specifications:


Laboratory panel flange with polished chrome plated body, ball valve hose cock for gas, air or vacuum with serrated tip outlet (accepts 1/4" to 3/8" I.D. hose), lever handle and 3/8" NPT female inlet. Certified to Z21.15a / CSA 9.1a. Meets ADA ANSI/ICC A117.1 requirements.

Job Name	
Model Specified	Quantity
Variations Specified	
Date	









- · Laboratory panel flange with polished chrome plated body
- Ball valve hose cock w/ serrated tip (accepts 1/4" to 3/8" I.D. hose)
- Lever handle
- · Hose cock for gas, air or vacuum
- For natural gas above 0.5 psig or Oxygen and specialty gases, use BL-4010-01 gas cock
- · Natural gas (dark blue) snap-in index included
- Air (orange) Snap-in index included
- Vacuum (yellow) snap-in index included
- Ø 2" panel flange w/ 3/8" NPT female inlet
- Material: Polished chrome plated brass panel flange & ball valve hose cock

Product Compliance:

- ANSI Z21.15a / CSA 9.1a
- ANSI A117.1 (ADA)



ADA Compliant

Warranty: One Year (Limited)

Performance Data:

- Pressure:
 - Gas 0.5 psig max
 - Air 125 psig max
 - Vacuum 30 inches of Mercury max
- Temperature: 32 °F 125 °F



