


TAG:

Swivel Pantry Faucet

Architect/Engineering Specifications:

8" wall mount mixing faucet with polished chrome plated brass body, built-in service stops in body, 12" swing nozzle with stream regulator outlet, compression cartridges with spring checks, lever handles and 1/2" NPT female inlets. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements.



Features & Benefits:

- 8" wall mount mixing faucet with polished chrome plated brass body
- Built-in service stops in body
- 12" swing nozzle
- · Lock washer provided for rigid application
- Stream regulator outlet, Series 1
- Quarter-turn Eterna compression cartridges w/ spring checks to prevent the cross flow of water
- · Lever handles w/ color coded indexes
- 1/2" NPT female eccentric inlets w/ Ø 2" flanges
- Adjustable centers from 7 3/4" to 8 1/4"
- Material: Polished chrome plated brass body & tubular spout and chrome plated metal handles

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)

Warranty: One Year (Limited)

Performance Data:

- Pressure: 20 125 psi
- Temperature: 40 °F 140 °F
- Flow Rate: 22.5 GPM @ 60 psi

Optional Outlets	(Series 1 /)	VR Series 6	۱
optional outloto		111 001100 0	,

		Non-Aerated		VR Non-Aerated	Optional Cartridges With Checks
GPM	Aerated	(Laminar)	VR Aerated	(VR Laminar)	Quarter-Turn Cerama w/ Check Valve
0.35	N/A	□ B-0199-01-N035	N/A	□ B-0199-06-N035	Quarter-Turn Eterna w/ Spring Check (Standard)
0.5	N/A	□ B-0199-01-N05	N/A	□ B-0199-06-N05	Optional Handles
1.0	□ B-0199-01-F10	N/A	□ B-0199-06-F10	N/A	Optional nativies
1.2	□ B-0199-01-F12	□ B-0199-01-LF12	□ B-0199-06-F12	□ B-0199-06-LF12	4" Wrist Action
1.5	□ B-0199-01-WS	□ B-0199-29	□ B-0199-06-WS	□ B-0199-29VR	□ Lever (Standard)
2.2	□ B-0199-01	□ B-0199-21	□ B-0199-06	□ B-0199-21-VRF	□ 4-Arm









